




SPECIFICATION

Current Rating:3A
Dielectric Withstanding Voltage:1000V AC/Minute
Contact Resistance:20 Milliohms Max
Insulation Resistance:5000 Megaohms Min.At 500V DC
Operation Temperature:-55℃~+125℃
Insertion Force:0.4Kgf Max.Per Pair
Withdrawal Force:0.25Kgf Max.Per Pair

Insulator:PBT+G.F. (UL94V-0)
Contact:Brass or Phosphor Bronze
Gold Plated On Contact Area
Tin Plated On Solder Tails,Over Nickel

RoHS Compliant

Order Information

E D 98K B GF BK

E=2.54mm FEMALE EDGE SLOT
D=DIP STRAIGHT 180°
NO. OF PINS:98Pin WITH POLARIZING
BK=Black
GN=Green
BU=Blue
GF=1u" Glod Flash
03=3u" Glod
05=5u" Glod
10=10 u" Glod
15=15 u" Glod
A3=3u" All Glod

WingTAT® 深圳市格林柏电子技术开发有限公司			
X. ± 0.30	APPD:	PART NO: ED98KBGFBK	
.X ± 0.20	CHKD:		
.XX ± 0.10	HzF		
.XXX± 0.05	DR:		
X° ± 1°		DWG NO:	
.X° ± 0.5°			
UNITS: mm		SCALE: 1:1	SHEET 1 OF 1
			REV: A

REV	ECN NO	DESCRIPTION	DATE
A			