

printed on 4 Jan 2022 16:33 (China Standard Time) from TE152312

D

A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



© COPYRIGHT 20

BY -



ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	15MAY2015	DW	CW
	A1	ECR-16-015170	11JAN2017	YC	CW
	B	ECR-19-018087	22NOV2019	YC	CW
	B1	ECR-21-125167	4JAN2022	GY	CW





TYPE 1:
CSF-10 T2400002100-000
类型 1:
CSF-10 T2400002100-000






NOTES:
1. TECHNICAL CHARACTERISTICS:
CONTACT MATERIAL: BRASS
SURFACE PLATING:
SILVER PLATING: $\geq 2\mu\text{m}$
CONTACT RESISTANCE: $\leq 1.5\text{m}\Omega$
WIRE RANGE: 6.0-25mm²

注释:
1. 技术参数:
公针材料: 黄铜
表面电镀:
镀银: $\geq 2\mu\text{m}$
接触电阻: $\leq 1.5\text{m}\Omega$
接线范围: 6.0-25mm²



TYPE 2:
CSF-16 T2400002160-000
类型 2:
CSF-16 T2400002160-000



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID WANG 15MAY2015	 TE Connectivity		
DIMENSIONS: mm		CHK CHRIS WANG 15MAY2015			
		APVD XIANG XU 15MAY2015			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-137059			
0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ - 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ -		APPLICATION SPEC 114-137059	NAME CSF SS SOCKET CONTACT		
MATERIAL -		WEIGHT -	SIZE A3	CAGE CODE 00779	RESTRICTED TO -
FINISH -		CUSTOMER DRAWING	SCALE 3:2	SHEET 1 OF 2	REV B1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20





© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





TYPE 3:
CSF-25 T2400002250-000
类型 3:
CSF-25 T2400002250-000

NOTES:
SEE SHEET 1.
注释:
见SHEET 1.



TYPE 4:
CSF-6.0 T2400002060-000
类型 4:
CSF-6.0 T2400002060-000



T2400002100-000	CSF-10	CSF-10,SILVER PLATING / SS母针 10mm ² , 镀银	4.3	5.6	10	15	TYPE 1
T2400002160-000	CSF-16	CSF-16,SILVER PLATING / SS母针 16mm ² , 镀银	5.5	8.5	16		TYPE 2
T2400002250-000	CSF-25	CSF-25,SILVER PLATING / SS母针 25mm ² , 镀银	7.0	10.0	25		TYPE 3
T2400002060-000	CSF-6.0	CSF-6.0,SILVER PLATING / SS母针 6.0mm ² , 镀银	3.5	5.0	6		TYPE 4
PART NUMBER 料号	PART DESCRIPTION 描述		ØA	ØB	WIRE GAUGE 线规(mm ²)	STRIPPING LENGTH(mm) 剥线长度	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.


DWN 15MAY2015
DAVID WANG
CHK 15MAY2015
CHRIS WANG
APVD 15MAY2015
XIANG XU



TE Connectivity

NAME
CSF
SS SOCKET CONTACT

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

-
-

FINISH

-
-

PRODUCT SPEC
108-137059

APPLICATION SPEC
114-137059

WEIGHT

-

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-T2400002XX0000

CUSTOMER DRAWING

SCALE

3:2

SHEET

2 OF 2

REV

B1