


Dimensions: [mm]



Electrical Properties:


Properties	Impedance 1 turn (Ω)	Impedance 1 turn (Ω)	Impedance 2 turn (Ω)	Impedance 2 turn (Ω)	Cable $\varnothing$ (mm)
Value	195	258	354	568	≤ 7.6
Tolerance	$\pm 25\%$	$\pm 25\%$	typ.	typ.	
Test Condition	25MHz	100MHz	25MHz	100MHz	

Storage Temperature (in original packaging): -20 °C to +60 °C

Operating Temperature: -25 °C to +125 °C

Typical Electrical Characteristics:

Impedance VS. Frequency Characteristics:



				UNIT: MM	KOHER_{elec} KOHER (Shanghai) Electronic Co.,Ltd
				SCALE:	
				SHEET: 1/1	
				APPROVAL: HY	
				SIZE:	DESCRIPTION: EMI Suppression Axial Ferrite Ring
A	16-SEP-19	PDF	CY	PACKING UNIT:	PART NO: AFBR081629-07
REV	DATE	FILE	BY		