


REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	21. 11. 22	SQW



技术要求:

- 电气特性: 使用矢量网络分析仪100%测试。  
特性阻抗:50Ω; 适用频率范围:824MHz-960MHz&1710MHz-2690MHz; 驻波比:最大4.00;
- 尺寸检验: [\*]为FAI检测项目; \*为重点检测项目; ■为CPK管制项目。
- 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污;镀层色泽光亮均匀, 不得有氧化。
- 包装规范: 50PCS/装封口
- 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS
7	2YGXXX	铜管	1	---
6	2SBKG0700	天线杆套, 13*L154, TPEE, 黑色	1	---
5	2SBKU31N8	CD384上固, OD: 13.00*L28.2mm, PC, 黑色	1	---
4	2SBKD36N3	CD13小孔下固, OD: 13.0*L25.3mm, PC+PBT, 黑色	1	---
3	2LC15PM804-5	SMA 公针OD: 1.5*L10.2mm, 镀金2u''	1	---
2	2LC15PF031-8	SMA公头OD13.0*L16.6	1	---
1	2C5R17813BN1	RG178透明棕双银线-50 OHM	1	---

GENERAL TOLERANCE:

LINEAR:	
X	±0.20
X.X	±0.15
X.XX	±0.05
X.XXX	±0.01

ANGLE:	
X°	±4.00°
X.X°	±3.00°
X.XX°	±2.00°
X.XXX°	±1.00°

HJ-Tech 东莞市皇捷通讯科技有限公司	
FILE NAME: 产品图	TITLE: 射频天线组件
ENG/DATE: SQW/21. 11. 22	直连式外置天线, G07黑色, RG178+SMA公头公针 (4GHz天线)
CHE/DATE:	P/N: RF2111027
APP/DATE:	UNIT: mm
	SCALE: 1:1
	REVISION: A0
	SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □HF; □SONY SS-00259; □OTHERS  
\*NO USING ESTRICED AND BANNED SUBSTANCE