THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 19 ALL RIGHTS RESERVED.

LOC	DIST
DS	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REVISED ((ECR-17-016272)	19.FEB.'18	KT	YJ







3D VIEW
SCALE 2:1

NOTES;

1. MATERIAL: CuNiSi ALLOY
2. FINISH: PRE-TIN PLATED
3. GENERAL TOLERANCE: ±0.2, ±3°
4. THIS PRODUCT IS DESIGNED TO BE COMPATIBLE WITH UN-SEALED APPLICATIONS.
5. APPLICATOR FEED: 10.0
6. MATING TAB THICKNESS: 0.63±0.03
7. THREE SERRATIONS CENTERED IN WIRE BARREL
8. SEVEN SERRATIONS CENTERED IN WIRE BARREL
9. COMBINED BARREL AND SEVEN SERRATIONS



SECTION B-B



SECTION C-C

PRELIMINARY - NOT RELEASED YET







SECTION A-A



SECTION B-B







SECTION C-C

MISSING DIMENSIONS ARE SAME WITH THREE SERRATIONS

7	(2.9)	2.8	Ø1.7	(2.3)	2.2	Ø1.1	1.4 - 1.9	0.5 - 0.75SQ	2	1	060 REC GOLD (S)	1-2109006-2
7	(2.45)	2.4	Ø1.3	(1.7)	1.7	Ø0.8	1.0 - 1.5	0.22 - 0.35SQ	2	1	060 REC GOLD (SS)	1-2109006-1
8	(3.75)	3.65	Ø2.0	(2.95)	2.6	Ø1.3	Ø1.8	AL 1.25SQ	2	1	AL 060 REC (M)	8-2109006-3
8	(2.9)	2.8	Ø1.7	(2.3)	2.2	Ø1.1	Ø1.4	AL 0.75SQ	2	1	AL 060 RECEP (S)	8-2109006-2
9	(2.65)	2.52	Ø1.4	(2.35)	2.12	Ø1.1	Ø1.4	AL 0.75SQ	2	1	AL 060 RECEP	9-2109006-2
7	(3.75)	3.65	Ø2.0	(2.95)	2.6	Ø1.3	1.8 - 2.4	0.85 - 1.25SQ	2	1	060 RECEP. (M)	2109006-3
7	(2.9)	2.8	Ø1.7	(2.3)	2.2	Ø1.1	1.4 - 1.9	0.5 - 0.75SQ	2	1	060 RECEP. (S)	2109006-2
7	(2.45)	2.4	Ø1.3	(1.7)	1.7	Ø0.8	1.0 - 1.5	0.22 - 0.35SQ	2	1	060 RECEP. (SS)	2109006-1
SHAPE	(F)	E	ØD	(C)	B	ØA	INSUL RANGE	WIRE RANGE	FINISH	MATERIAL	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL 1

FINISH 2

DWN KT JUNG
CHK KT LIM
APVD HG CHO
PRODUCT SPEC 108-61116
APPLICATION SPEC 114-61036
WEIGHT -

TE Connectivity

NAME .060 RECEP. CONTACTS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2109006	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV A4