






Electrical Characteristics:
Coil Resistance: 144 Ohm
Resistor in Parallel with Coil: 1000 Ohm
Equivalent Resistance: 125.9 Ohm $\pm$ 10%

Nominal Voltage: 12V
Pull-in Voltage: 7,2 V *)
Dropout Voltage: 1.6V *)
Temperature Range: -40°C to +125°C

*) Coil at Ambient Temperature

Terminal Shape	(1,2) with 4.8x0.8
Terminal Shape	(3,5) with 6.3x0.8
	Material / Colour
Cover	PA66 GF25 / Black
Terminal	3, 5 ECu57 / Sn
	1, 2 CuSn4 / Sn

PART NUMBER	MANUFACTURER PART NUMBER
2-1414971-4	V23074-H1005-A502-SZ-CBOX

PROPRIETARY					CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD					PAPER SIZE A2	
THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES, ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.											
APPLICABLE SPEC.:					FINISH						
					DIMENSIONS APPLY					PLATING	
					TOLERANCE UNLESS SPECIFIED OTHERWISE Tol. ISO 8015 ISO 2768 - v1		 DIMENSIONS IN MM		SCALE 2:1; 5:1		WEIGHT
									MATERIAL		---
					DATE	NAME		PART NAME			
				DWN.	11FEB2013	H.Franc.		MICRO A HC RELAY			
				APP.							
B3	ECO-21-004021	26MAR2021	HMF	REV.							
B2	ECO-17-015150	16OCT2017	HMF	LOCATION	PE EVORA						
B1	ECO-16-006646	29APR2016	HMF			DWG NO.			SHT.		
B	ECO-15-013609	22SEP2015	HMF			V23074-H1005-A502			1		
A	INITIAL VERSION	21FEB2013	HMF						OF 1		
REV. CHANGE ORDER		DATE	APP.	CLASS 1			CUSTOMER DRAWING				